


OPERATING INSTRUCTIONS

THE PUMP: This pump is a totally enclosed, submersible dewatering unit. It is powered by a 1/3 HP, 12 volt DC 30 AMP motor. Battery clips on the power cord allow easy connection to any 12 volt vehicle battery.

SWITCHING: The on-off switch is located on the power cord.

CONNECTING TO BATTERY: When connecting the clips to a battery, arcing is eliminated by keeping the on-off switch in the "off" position. Connect the red battery clamp to the positive (+) battery terminal. Connect the black battery clamp to ground: preferably on the vehicle's engine to a solid, metallic, stationary point. The connection should be at least 18 inches (480mm) from the battery.



HOSE: Since the pump develops relatively low pressure, it is recommended that non-collapsible hose be used for maximum pumping rates.

HOISTING & LOWERING: Attach a line to the metal handle on the top of the pump for hoisting or lowering the unit. **Do not use power cable for handling unit.**

TO OPERATE: Lower unit into liquid to be pumped and activate switch. Pump can be run for a few minutes without liquid, however, **do not run completely dry for extended periods.** Damage to shaft seal may result.

RUNNING TIME: This unit draws about 30 amperes and can be operated about 1 hour on a fully charged 55 AMP-hour battery and still permit starting of vehicle under normal conditions. Caution should be used when running time exceeds 30 or 40 minutes without engine running to recharge battery, particularly in cold weather when battery efficiency is lowered. Battery size (AMP-hour rating) and the use of other accessories such as lights and radios, etc., must be taken into consideration for practical running periods without engine running.

OVERLOAD PROTECTION is provided by means of a 40 amp automatic reset circuit breaker, located under top cover.



! IMPORTANT

Read these safety warnings and instructions in this manual completely, before installation and start-up of the pump. It is the responsibility of the purchaser to retain this manual for reference. Failure to comply with the recommendations stated in this manual will damage the pump, and void factory warranty.



! DANGER

Turn off before connecting battery clamps to battery. Arcing could result.



! DANGER

DANGER: Not for use with fluids that have a flash point below 100° F (38° C) [examples: gasoline, alcohol.] Sparking could result in death.



! IMPORTANT

Should unit not operate, always check freeness of rotation of impeller by inserting screwdriver through hole in base plate into slot in end of shaft.



TROUBLE SHOOTING

NOTE: Most common cause of failure to run is due to hardened mud and sand at impeller. Remove strainer to check.

MOTOR WILL NOT RUN:

1. Poor connection at battery.
2. Impeller locked with foreign material.
3. Insufficient impeller clearance.
4. Damaged power cable or loose connection internally in motor assembly.
5. Bad switch or circuit breaker. Connect power leads direct to motor leads to check.
6. Worn motor brushes or out of position to make contact with armature.

PERFORMANCE LOW:

1. Strainer screen partially plugged.
2. Impeller rubbing. Check freeness of rotation with screwdriver inserted through hole in base plated into slotted end of shaft.
3. Battery not fully charged.
4. Discharge restriction such as kinked hose or excessive discharge head.

Motor runs backwards:

1. Check wiring for correct polarity.




SERVICE AND REPAIR INSTRUCTION

DISASSEMBLY: Impeller and shaft seal can be inspected and serviced from lower end of pump by removal of 4 capscrews securing base plate, strainer screen, and suction cover. Screwdriver slot is provided in end of motor shaft to turn shaft while holding impeller for removal. This permits removal of impeller without disassembly of upper motor housing to hold motor shaft. Alternately, there is a shaft extension with two flats on the rear of the motor for use when the impeller is difficult to remove. The upper motor cover must be removed to expose this shaft extension.

To service motor remove 4 hex nuts and bump top cover free from housing tube. Raise sufficiently to disconnect power cable connections. Slide housing tube up from pump casing and motor will be exposed for service or removal.

When servicing the PortaPump and replacing the impeller (part number 444.001.010.) or suction cover (part number 258.001.157.) follow these instructions: The impeller has been revised to typically require 1 shim (previously 7). The suction cover has been revised to require 1 gasket (previously 5).

IMPORTANT: Make certain that wire leads are installed per diagram below. Install top cover as indicated by arrow and instruction on top of cover. Make sure wires do not contact motor shaft when installing motor cover.



WARRANTY

This unit is guaranteed for a period of 5 years against defective material and workmanship.



SERVICE AND OPERATING MANUAL

PortaPump® Model SPA 1½-E

Model SPA40-E

Design Level 3

ITEM NO.	PART NUMBER	DESCRIPTION	TOTAL RQD.
1	710-004-330	Screw, Self-Tapping	2
2	258-017-157	Cover, Motor	1
3	545-005-330	Hex Nut	1
4	405-009-000	Handle	1
5	543-001-162	Nut, Gland	2
6	770-007-162	Spacer, Gland	2
7	675-016-360	Ring, Sealing	2
8	545-004-330	Hex Nut	4
9	900-004-330	Lock Washer	4
10	807-011-330**	Stud	4
11	270-001-000	Circuit Breaker	1
12	170-028-330	Capscrew, Hex Head 1/4-20 X .875	4
13	900-001-330	Lock Washer	8
14	360-001-440	Gasket, Casing	1
15	170-003-115	Capscrew, Hex Head 1/4-20 X 2.75	4
16	444-001-010	Impeller	1
17	740-001-115	Shim	As. Req.*
18	258-001-157	Cover, Suction	1
19	<u>612-001-156</u>	Plate, Strainer	1
20	700-001-330	Screen, Strainer	1
21	181-001-155	Casing, Volute, 1½ NPT	1
	181-001-155E	Casing, Volute, 1½ BSPT (tapered)	1
22	560-022-360	O-Ring	2
23	720-005-000	Seal	1
24	860-011-150**	Tube, Casing	1
25	525-005-000	Motor	1
26	200-003-000	Clamp, Cable	1
27	706-007-330	Screw, Machine	1
28	150-036-000	Power Cable Assembly Complete	1
29	900-002-330	Washer, Lock	1
30	510-003-000	Lug, Compression	1
31	240-001-000	Nut, Insulated Wire	1
For Models SPA153F, 12DC3 and SPA15BSP3F, 12DC3: (Not Shown)			
10	807-011-330	Stud	2
	807-012-330	Stud (replaces 2 807-011-330)	2
	325-001-330	Foot, Mounting	2
	547-001-330	Stop Nut 5/16-18Vac	2
	904-001-330	Washer	2
Service Items: (Not Shown)			
	475-220-000	Design Level 2 to Design Level 3 Conversion Kit	

Repair Parts shown in **bold face (darker)** type are more likely to need replacement after extended periods of normal use. They are readily available from most Warren Rupp distributors. The pump owner may prefer to maintain a limited inventory of these parts in his own stock to reduce repair downtime to a minimum.

IMPORTANT: When ordering repair parts always furnish pump model number, serial number and type number.

MATERIAL CODES	
The Last 3 Digits of Part Number	
000...Assembly, sub-assembly; and some purchased items	
010...Cast Iron	
012...Powered Metal	
015...Ductile Iron	
020...Ferritic Malleable Iron	
025...Music Wire	
080...Carbon Steel AISI B-1112	
100...Alloy 20	
110...Alloy Type 316 Stainless Steel	
111...Alloy Type 316 Stainless Steel (Electro Polished)	
112...Alloy "C"	
113...Alloy Type 316 Stainless Steel (Hand Polished)	
114...303 Stainless Steel	
115...302/304 Stainless Steel	
117...440-C Stainless Steel (Martensitic)	
120...416 Stainless Steel (Wrought Martensitic)	
123...410 Stainless Steel (Wrought Martensitic)	
148...Hardcoat Anodized Aluminum	
149...2024-T4 Aluminum	
150...6061-T6 Aluminum	
151...6063-T6 Aluminum	
152...2024-T4 Aluminum (2023-T351)	
154...Almag 35 Aluminum	
155 or 156...356-T6 Aluminum	
157...Die Cast Aluminum Alloy #380	
158...Aluminum Alloy SR-319	
159...Anodized Aluminum	
162...Brass, Yellow, Screw Machine Stock	
165...Cast Bronze, 85-5-5-5	
166...Bronze SAE 660	
170...Bronze, Bearing Type, Oil Impregnated	
180...Copper Alloy	
310...Kynar Coated	
330...Zinc Plated Steel	
331...Chrome Plated Steel	
332...Electroless Nickel Plated	
335...Galvanized Steel	
336...Zinc Plated Yellow Brass	
337...Silver Plated Steel	
340...Nickel Plated	
342...Filled Nylon	
354...Injection Molded #203-40 Santoprene - Duro 40D ± 5; Color: RED	
355...Thermoplastic Elastomer	
356...Hytrel	
357...Rupplon (Urethane Rubber) Color coded: PURPLE	
358...Rupplon (Urethane Rubber) Color coded: PURPLE (Some Applications, Compression Mold)	
359...Urethane Rubber	
360...Buna-N Rubber Color coded: RED	
361...Buna-N	
363...Viton (Fluorel) Color coded: YELLOW	
364...E.P.D.M. Rubber Color coded: BLUE	
365...Neoprene Rubber Color coded: GREEN	
366...Nitrile, USDA Approved	
368...EPDM, USDA Approved	


List continued next page

Parts underlined are only available for sale in kits

Parts that are boxed are not available for sale

* Typically 1

** Items 10 & 24 available as a kit #475-132-000



Repair Parts shown in **bold face (darker)** type are more likely to need replacement after extended periods of normal use. They are readily available from most Warren Rupp distributors. The pump owner may prefer to maintain a limited inventory of these parts in his own stock to reduce repair downtime to a minimum.

IMPORTANT: When ordering repair parts always furnish pump model number, serial number and type number.

MATERIAL CODES **The Last 3 Digits of Part Number**

Continued from previous page

370...	Butyl Rubber Color coded: BROWN
371...	Phlithane (Tuftane)
375...	Fluorinated Nitrile
378...	High density Polypropylene
405...	Cellulose Fibre
408...	Cork and Neoprene
425...	Compressed Fibre
426...	Blue Gard
440...	Vegetable Fibre
465...	Fibre
500...	Delrin 500
501...	Delrin 570
505...	Acrylic Resin Plastic
520...	Injection Molded PVDF Natural Color
540...	Nylon
541...	Nylon
542...	Nylon
544...	Nylon Injection Molded
550...	Polyethylene
551...	Polypropylene
552...	Unfilled Polypropylene
553...	Unfilled Polypropylene
555...	Polyvinyl Chloride
570...	Rulon II
580...	Ryton
590...	Valox
591...	Nylatron G-S
592...	Nylatron NSB
600...	Virgin PTFE Tetrafluoroethylene (TFE)
601...	Virgin PTFE (Bronze and moly filled)
602...	Filled Virgin PTFE
603...	Blue Gylon
604...	Virgin PTFE
606...	Virgin PTFE
610...	Virgin PTFE Encapsulated Silicon
611...	Virgin PTFE Encapsulated Viton

Delrin, Viton and Hytrel are registered trademarks of E.I. DuPont.

Gylon is a registered trademark of Garlock, Inc.

Nylatron is a registered trademark of Polymer Corp.

Rulon II is a registered trademark of Dixon Industries Corporation.

Hastelloy-C is a registered trademark of Cabot Corp.

Ryton is a registered trademark of Phillips Chemical Company.

Valox is a registered trademark of General Electric Company.

Rupplon, SandPIPER, PortaPump, Tranquilizer, SludgeMaster and Warren Rupp are trademarks of Warren Rupp, Inc.

INSTRUCTIONS FOR HANDLE CONVERSION

